




CARBON CARTRIDGES: WATER


CARBONEX - W: 3 in 1 GRANULAR CARBON FILTER



- Substantially reduce or remove chlorine and other chemicals, tastes, odors and sediment.
- 2 U.S. GPM per each 10" length.
- 3 - Step Filtration
 - 50 Micron Polyethylene prefilter.
 - Activated Carbon absorption bed.
 - 3 Micron Polypropylene depth wound polishing filter.
- EPDM End Gaskets.

MODEL	WEIGHT	LENGTH	DIA	QTY PER CARTON
CU9.8W	7 oz.	9 - 3/4"	2-3/4"	25
CU19.8W	14 oz.	19 - 3/4"	2-3/4"	12

CARBO-FYNE - W: POWDERED CARBON FILTER



- 3 U.S. GPM per each 10" length.
- Substantially reduce or remove chlorine taste and organic related odors and colors.
- 10 Micron retention assures turbidity-free water.
- Polypropylene core with polyethylene end caps and polyolefin white net.

MODEL	WEIGHT	LENGTH	DIA	QTY PER CARTON
C4W	1.6 oz.	4"	2-3/4"	60
C10W	4 oz.	9.75"	2-3/4"	30
C20W	8 oz.	19.75"	2-3/4"	30


CARBO-WIND - W: 3 in 1 GRANULAR CARBON FILTER



- 2.5 U.S. GPM per each 10" length
- 3 in 1 removal of sediment, chlorine, chemicals, unpleasant tastes and odor.
- Depth-Wound polypropylene prefilter provides maximum sediment removal
- Encased bed of granular activated carbon, followed by 3 Micron depth wound polishing filter.

MODEL	WEIGHT	LENGTH	DIA	QTY PER CARTON
CU9.8UW	5 oz.	9 3/4"	2-3/4"	20
CU19.8UW	10 oz.	19 3/4"	2-3/4"	12

MAXI-CARB - W: POWDERED CARBON FILTER



- Absorbs undesirable contaminants including chlorine and many organics.
- Serves as an effective sediment removal filter down to the 1 - 2 micron range.
- Non-Metallic, polyethylene end caps w/ rubber gaskets, polyolefin blue net, and polypropylene core.
- Cartridge contains high purity, pre-washed, and sulfur-free pulverized activated carbon.
- 3 U.S. GPM flow rate.

Designed to fit SERFILCO GPO10-1 chamber. See Bulletin C-101

MODEL	WEIGHT	QTY PER CARTON
C510W	17 oz.	12

Maximum operating temperature: 180°F (82°C)



CARBON CARTRIDGES: WATER

MINI CANISTER - W: POWDERED CARBON FILTER



MODEL	WEIGHT	3" DIA. x LENGTH
10ABS	14 oz.	10"
20ABS	33 oz.	20"

*Carbon and Resin sold separately
Maximum operating temperature: 160°F (71°C)

Designed to fit SERFILCO GPO and GSO chambers. See Bulletin C-101

GRANULAR ACTIVATED CARBON		
COCONUT SHELL BASED		
Steam activated for high absorption capacity		
12 x 30 MESH STANDARD	LBS	PCN
	10	99-0997-10
	50	99-0997-50

To order resin, refer to bulletin R-208