

# X Series

## Fluoropolymer Immersion Coil

### PRODUCT DATA SHEET

All wetted parts of fluoropolymer

Heavy wall tubing improves circulations and reduces pressure drop

Eliminates stray currents in the tank

Integral inlet/outlet connections reduce potential for leaks



Sizes: 4.5 ft<sup>2</sup> to 46.5 ft<sup>2</sup>



FEP for up to 30 PSI steam service, PFA for up to 60 PSI

EXCHANGE CONNECTIONS		DIMENSIONS					MODEL NUMBER	SHIP WGT.
AREA Sq. Ft.	In.	A In./(mm)	B In./(mm)	C In./(mm)	D In./(mm)	E In./(mm)		Lbs./(kg)
4.5*	1/2" FNPT	11½ (292)	11½ (292)	2 (51)	17½ (445)	8 (203)	X2-12-12-18-F	11 (5)
4.5*	1/2" FNPT	15½ (394)	15½ (394)	1½ (38)	21½ (546)	12 (305)	X2-16-16-22-F	13 (6)
9.25*	1/2" FNPT	15½ (394)	15½ (394)	2 (51)	21½ (546)	12 (305)	X4-16-16-22-F	14 (6.5)
6.00	1" FNPT	17½ (445)	17½ (445)	2 (51)	23½ (597)	12½ (318)	X2-18-18-24-F-LP	18 (8)
12.00	1" FNPT	17½ (445)	17½ (445)	3¼ (82.5)	23½ (597)	12½ (318)	X4-18-18-24-F-LP	22 (10)
18.00	1½ FNPT	17½ (445)	17½ (445)	4½ (114)	23½ (597)	12½ (318)	X6-18-18-24-F-LP	26 (12)
24.00	1½ FNPT	17½ (445)	17½ (445)	5¾ (146)	23½ (597)	12½ (318)	X8-18-18-24-F-LP	30 (13.5)
11.50	1" FNPT	23½ (597)	23½ (597)	2 (51)	29½ (750)	18½ (470)	X2-24-24-30-F-LP	24 (11)
23.00	1" FNPT	23½ (597)	23½ (597)	3¼ (82.5)	29½ (750)	18½ (470)	X4-24-24-30-F-LP	30 (13.5)
34.50	1½" FNPT	23½ (597)	23½ (597)	4½ (114)	29½ (750)	18½ (470)	X6-24-24-30-F-LP	36 (16.5)
46.50	1½" FNPT	23½ (597)	23½ (597)	5¾ (146)	29½ (750)	18½ (470)	X8-24-24-30-F-LP	42 (19)

Minimum pressure 10 PSI. \*Mini coils are not suitable for liquid.

**PROCESS  
TECHNOLOGY**

## Features & Values


- All wetted parts of fluoropolymer (FEP, PFA or PTFE) construction with a heavy duty CPVC mounting bracket.
- Heavy wall tubing improves circulation and minimizes pressure drop. Larger coils constructed of 1/2 inch (13mm) tubing, smaller coils have 1/4 inch (7mm) tubing.
- Integral inlet and outlet manifolds for single point connections greatly reduce the potential for leaks and simplify installation.
- Eliminates stray currents in the tank.

## Specifications

<b>Sizes</b>	4.5 ft <sup>2</sup> to 46.5 ft <sup>2</sup> exchange area
<b>Pressure</b>	Standard coils: FEP up to 30 PSI steam pressure PFA (Perfluoroalkoxy resin) up to 60 PSI steam service
<b>Options</b>	<ul style="list-style-type: none"> <li>◆ Anti-floatation brackets</li> <li>◆ Special manifold connections</li> <li>◆ Custom &amp; bottom configurations</li> <li>◆ Dual coils for heating &amp; cooling</li> </ul>

**NOTE:** Vacuum breakers recommended for fluoropolymer immersion coil steam installations. Please consult factory regarding pressure reduced steam applications.

## Dimensions



## Model Number Breakdown

Series	Number of Tubes	Coil Height (Inches)	Coil Width (Inches)	"D" Dimension (Inches)	Type of Material	Options
X = Fluoropolymer	2	12 = 11.5"	12 = 11.5"	18 - 17.5"	F = FEP	-LP = low pressure manifold (standard)
	3	16 = 15.5"	16 = 15.5"	22 - 21.5"	P = PFA	-A = connections up
	4	18 = 17.5"	18 = 17.5"	24 - 23.5"		-B = connections to left and right sides
		24 = 23.5"	24 = 23.5"	30 - 29.5"		-BR = bottom riser (specify riser height)
		XX = specify	XX = specify	Std cold zone is 6"		